

tekmar® - Job Record

Zone Manager 336



J336

08/09


Control Name / Location _____ Connected to Module _____

Zone Group A	External tN4 Input / Output	Zone Group Pump A Input	Zone	A1	A2	A3	A4
Control Label			Label				
Model			Thermostat Model				
Location			Schedule Heat / Cool				
Bus #			Cool Group				
			Address				

VA from left side module = _____ + VA _____ + _____ + _____ = _____

Total Tstat + Left Side Module VA

Max. 24 VA
24 V (ac)
See W336 to add extra VA



Dip Switch Settings
(circle / fill-in the correct setting)

Zone Group Pump A

A1	On	Off
A2	On	Off
A3	On	Off
A4	On	Off

Line Voltage Input	Zone Group Pump	A	Line Voltage Input	Zone Pump	A1	A2	A3	A4
115 V (ac)	Label		115 V (ac)	Label				
	Make		use separate breaker if required	Make				
	Model			Model				
Combined Total Amps	Amps	(Max. 5 A)	Amps	Amps	(Max. 5 A)	(Max. 5 A)	(Max. 5 A)	(Max. 5 A)
Max. 11.7A	Design Flow		If using same power as terminals 20-21 then add to the left	Design Flow				
	Design Head			Notes				

If using separate power then add to the right

Total Zone Pump Amps
115 V (ac)

Max. 12 Amps on separate breaker

Notes:

Blank job records can be downloaded from the tekmar website at <http://www.tekmarcontrols.com>



tekmar Control Systems Ltd., Canada
tekmar Control Systems, Inc., U.S.A.
Head Office: 5100 Silver Star Road
Vernon, B.C. Canada V1B 3K4
(250) 545-7749 Fax. (250) 545-0650
Web Site: www.tekmarcontrols.com

