



Industrial-Strength Butterfly Valves

For Facilities Seeking Optimal Performance 24/7

SERIES 88

Ductile Iron Full Lug Butterfly Valves

Equally effective for on-off, throttling, or isolation service requirements.

- Designed for dead-end service to the full pressure rating of the valve
- Well suited for higher velocity and vacuum service
- Blowout-proof stem
- Operated by lever handle, IP67 rated gear operator or electric actuator.
- Lug style, ductile iron body with stainless steel stem and disc
- Sized from 2" to 60"

SERIES 88:
Shown with
Electric Actuator



SERIES 90

High-Performance Lug Double Eccentric Butterfly Valves

Used wherever positive shutoff is required to control flow.

- Double offset RPTFE seat designed for 500° F
- Guaranteed bubble-tight at 290 psi differential
- Operated by lever handle, IP67 rated gear operator or electric actuator.
- Lug style, carbon steel body with stainless steel stem and disc
- Sized from 2" to 40"

SERIES 90:
Shown with
IP67 Rated
Gear Operator



Optional electric actuator available on both valves enabling on/off and modulating service for precise flow control



Scan to Learn More

Mueller Steam Specialty™