


# Invita™ WiFi Thermostat



# Getting to know your thermostat

- The thermostat home screen displays all the information about the thermostat.
- After 60 seconds of inactivity, a standby screen is displayed with the time and temperature.
- Simply touch the screen to wake and return to the home screen.

## Invita WiFi Thermostat Display



### Symbols



The fan is on



The humidifier is on



The dehumidifier is on



The info button provides a description of the setting




Ok setting change




Cancel setting change

# Settings menu

Press the ⚙️ button to enter the settings menu



# Setup menu for advanced settings



# Programming a schedule

Schedule

Mon Tue Wed Thu Fri

Wake 6:00 AM 70° 75°

Leave 8:00 AM 65° 78°

Return 6:00 PM 70° 75°

Sleep 10:00 PM 65° 78°

Early Start On

Schedule On

✓ New Schedule ⓘ

Annotations:

- Current group of program days
- Go to the next group of program days
- Heating temperature
- Cooling temperature
- Early Start anticipates the time required to heat or cool a room and starts early
- Back to home screen
- Creates a new schedule

Schedule Setup

Mon Tue Wed Thu Fri

Wake  On  Skip

6:00 AM

Heat to 70°

Cool to 75°

✓ ▲ ▼ ⓘ

Annotations:

- Set to On to follow the schedule. Set to Off to use the same temperature all of the time.
- Select skip if you don't want a temperature change
- Set schedule start time
- Set heating temperature
- Set cooling temperature


# Setting up WiFi

## NOTICE

Before using the WiFi features of this product, you must accept the Terms of Use, as amended from time to time and available at [InvitaConnect.com/terms](http://InvitaConnect.com/terms). If you do not accept these terms, this product can still be used without WiFi features.

Incorrectly setting the time and date manually may prevent the thermostat from communicating to the mobile app. Automatic time source is recommended when using an Internet connection.

The thermostat includes a step by step tutorial to setup the WiFi connection.




Tutorial

Before first using wi-fi features of this product, you must accept the Terms of Use available at <http://InvitaConnect.com/terms> by pressing AGREE below.

If you do not accept these terms, this product can still be used without wi-fi features.

DISAGREE    AGREE

**Step 1**  
Agree to Terms of Use.




WiFi

Off  
 On

NEXT

**Step 2**  
Turn on WiFi.




NETWORK SSID

Select a network from the list:

Your House ▼

←    CONNECT

**Step 3**  
Enter wireless network name. It must support WPA2 security encryption.




Enter Password

[Empty password field]

A B C D E F  
G H I J K L  
M N O P Q R  
S T U V W X  
Y Z [Space] Shft A/1 Del

←    CONNECT

**Step 4**  
Enter WiFi password.




ZIP/Postal

[Empty ZIP field]

1 2 3 4 5 6  
7 8 9 0 - /  
: ; ( ) \$ &  
@ " ' , ? !  
' \ [Space] Shft A/1 Del

OK

**Step 5**  
Enter ZIP or postal code. This determines your location for weather information.



Time Source

Automatic  
 Manual


NEXT

**Step 6**  
Select if the time is set automatically from the Internet or manually.

# Mobile and Web App

To view and adjust the WiFi Thermostat using a mobile phone or tablet, download the Invita Connect mobile app from the Apple® Store or from the Google Play® Store.


Alternatively, go to [InvitaConnect.com](http://InvitaConnect.com) for web browser access.



The screenshot shows the Invita Connect login page. At the top is the Invita logo, a stylized 't' with a red triangle and a blue triangle. Below the logo is the text 'Invita™ Connect'. There are two input fields for 'Email' and 'Password'. Below these is a 'SIGN IN' button. A link for 'Forgot Password' is below the sign in button. Below that is the text 'Don't have an account?' followed by a 'SIGN UP AND GET STARTED' button. At the bottom is a link for 'Terms and conditions'.

## Step 1


Create a new account. Then login using your username and password.



The screenshot shows the 'Home' screen of the app. At the top is a blue header with 'Home' and a dropdown arrow. Below the header is a grey bar with 'HOME' and a plus sign. The main content area says 'You don't have any devices associated with this location.' and has an 'ADD A DEVICE' button. At the bottom is a navigation bar with 'My Devices' and 'Account' icons.

## Step 2

Add a Device



The screenshot shows the 'REGISTRATION' screen on a thermostat. At the top is the 'tekmar' logo. Below it is a grey bar with 'REGISTRATION'. The main text says 'To finish registering your thermostat, enter the code displayed below at [InvitaConnect.com](http://InvitaConnect.com)'. Below this is a grey box with the code '12345678'. At the bottom left is a back arrow icon.

## Step 3


On the thermostat, go to WiFi menu and press Register Device. The code is valid for 30 minutes.



The screenshot shows the 'Add a Device' screen. At the top is a blue header with a back arrow and 'Add a Device'. Below the header are three input fields: 'Registration code' with '12345678', 'Device Name' with 'Upstairs', and 'Location' with a dropdown menu showing 'Home'. Below these is an 'ADD DEVICE' button. At the bottom is a navigation bar with 'My Devices' and 'Account' icons.

## Step 4


- Enter the 8 digit number from the thermostat into the mobile app.
- Enter the thermostat's room name.
- Enter the building location name for the thermostat.



The screenshot shows the 'Edit Your Account' screen. At the top is a blue header with 'Edit Your Account'. Below the header are several input fields: 'Username' with 'name@domain.com', 'First & Last Name', 'Email Address', 'Phone' with a dropdown menu showing '(###)###-####', and 'Units' with 'F'. Below these is a 'Change Password' link and a 'SAVE' button. At the bottom is a 'Logout' link and a navigation bar with 'My Devices' and 'Account' icons.

## Step 5

Edit your account and save.



The screenshot shows the 'Home' screen of the app. At the top is a blue header with 'Home' and a dropdown arrow. Below the header is a grey bar with 'HOME' and a plus sign. The main content area shows 'Upstairs' with a temperature of '78 °F' and 'Auto'. At the bottom is a navigation bar with 'My Devices' and 'Account' icons.

The thermostat is now listed on the My Devices page.

# Using the App

Choose the building location

HOME  AWAY

Set to AWAY to save energy when you are away for a day or more

View and change thermostat

Home ▾

HOME  +

Upstairs 78 °F Heat

Basement 75 °F Heat

Master Bathroom 78 °F Heat

My Devices Account

Add a device

Edit location info

Edit account info

Change from Emergency Heat, Heat, Cool, Auto or Off mode

Change heating and cooling setting

Save temperature change to the schedule

Return to home view

Upstairs

Auto ▾

tekmar  
A WATTS Brand

HEAT TO 70°

COOL TO 76°

TEMP 72°

40° 100°

SAVE TO PROGRAM

CANCEL HOLD

My Devices Account

View and edit settings

View and edit schedule

Edit device info

Temperature change hold until schedule change

# Warranty

**Limited Warranty** *The liability of tekmar under this warranty is limited. The Purchaser, by taking receipt of any tekmar product ("Product"), acknowledges the terms of the Limited Warranty in effect at the time of such Product sale and acknowledges that it has read and understands same.*

The tekmar Limited Warranty to the Purchaser on the Products sold hereunder is a manufacturer's pass-through warranty which the Purchaser is authorized to pass through to its customers. Under the Limited Warranty, each tekmar Product is warranted against defects in workmanship and materials if the Product is installed and used in compliance with tekmar's instructions, ordinary wear and tear excepted. The pass-through warranty period is for a period of twenty-four (24) months from the production date if the Product is not installed during that period, or twelve (12) months from the documented date of installation if installed within twenty-four (24) months from the production date.

The liability of tekmar under the Limited Warranty shall be limited to, at tekmar's sole discretion: the cost of parts and labor provided by tekmar to repair defects in materials and / or workmanship of the defective product; or to the exchange of the defective product for a warranty replacement product; or to the granting of credit limited to the original cost of the defective product, and such repair, exchange or credit shall be the sole remedy available from tekmar, and, without limiting the foregoing in any way, tekmar is not responsible, in contract, tort or strict product liability, for any other losses, costs, expenses, inconveniences, or damages, whether direct, indirect, special, secondary, incidental or consequential, arising from ownership or use of the product, or from defects in workmanship or materials, including any liability for fundamental breach of contract.

The pass-through Limited Warranty applies only to those defective Products returned to tekmar during the warranty period. This Limited Warranty does not cover the cost of the parts or labor to remove or transport the defective Product, or to reinstall the repaired or replacement Product, all such costs and expenses being subject to Purchaser's agreement and warranty with its customers.

Any representations or warranties about the Products made by Purchaser to its customers which are different from or in excess of the

tekmar Limited Warranty are the Purchaser's sole responsibility and obligation. Purchaser shall indemnify and hold tekmar harmless from and against any and all claims, liabilities and damages of any kind or nature which arise out of or are related to any such representations or warranties by Purchaser to its customers.

The pass-through Limited Warranty does not apply if the returned Product has been damaged by negligence by persons other than tekmar, accident, fire, Act of God, abuse or misuse; or has been damaged by modifications, alterations or attachments made subsequent to purchase which have not been authorized by tekmar; or if the Product was not installed in compliance with tekmar's instructions and / or the local codes and ordinances; or if due to defective installation of the Product; or if the Product was not used in compliance with tekmar's instructions.

THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, WHICH THE GOVERNING LAW ALLOWS PARTIES TO CONTRACTUALLY EXCLUDE, INCLUDING, WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, DURABILITY OR DESCRIPTION OF THE PRODUCT, ITS NON-INFRINGEMENT OF ANY RELEVANT PATENTS OR TRADEMARKS, AND ITS COMPLIANCE WITH OR NON-VIOLATION OF ANY APPLICABLE ENVIRONMENTAL, HEALTH OR SAFETY LEGISLATION; THE TERM OF ANY OTHER WARRANTY NOT HEREBY CONTRACTUALLY EXCLUDED IS LIMITED SUCH THAT IT SHALL NOT EXTEND BEYOND TWENTY-FOUR (24) MONTHS FROM THE PRODUCTION DATE, TO THE EXTENT THAT SUCH LIMITATION IS ALLOWED BY THE GOVERNING LAW.

**Product Warranty Return Procedure** All Products that are believed to have defects in workmanship or materials must be returned, together with a written description of the defect, to the tekmar Representative assigned to the territory in which such Product is located. If tekmar receives an inquiry from someone other than a tekmar Representative, including an inquiry from Purchaser (if not a tekmar Representative) or Purchaser's customers, regarding a potential warranty claim, tekmar's sole obligation shall be to provide the address and other contact information regarding the appropriate Representative.

**Need help? Go to our website or contact us.**

tekmarControls.com | tekmar.customerservice@wattswater.com | 1-800-438-3903



**A WATTS Brand**