

# No Wire? No Problem



**Don't let your next installation come down to the wire**

The Wireless Outdoor Sensor 087 offers a simple solution for installations where wiring to the building exterior is challenging or undesired.

## Wireless Outdoor Sensor 087

- Compatible with both tekmar, and other control types
- 10K (type 2 and 3), 5K, 12K and 20K sensor settings
- Simply mount transmitter on building exterior, no drilling or wire routing required
- 5000 ft (1500 m) open range
- 8 wall / 250 ft (75 m) indoor range
- Long-life (min. 10 year) batteries included
- Outdoor unit rated for extreme temperatures of -40 to 140°F (-40 to 60°C)



Receiver



The 087 transmitter can be installed anywhere for the best possible temperature reading.

Transmitter



Contact your local tekmar representative or wholesaler to order today

All specifications are subject to change without notice.

Tel: (250) 545-7749 • Fax: (250) 984-0815  
tekmarControls.com

© 2016 tekmar

**tekmar**<sup>®</sup>

**A WATTS Brand**

P10057 - 06/16