

tekmar® - Job Record

Universal Reset Module 422




J422

08/09

Control Name / Location _____ Connected to Zone Manager _____

Terminals	DHW Demand	Setpoint Demand	24 V (ac) Auxiliary	External tN4 Input	Floating Action Motor	Boiler Modulation	Boiler Sensor	Mix 1 Sensor	Outdoor Sensor
Label									
Make									
Model									
Notes									
VA	+	+	N/A	+	N/A	N/A	N/A	N/A	N/A



Terminals	DHW Pump	Injection Pump	Primary Pump	Mixing System 1 Pump	Add Total Amps to Zone Manager Total
Label					
Make					
Model					
Amps	(Max. 5 A)	(Max. 2.5 A)	(Max. 5 A)	(Max. 5 A)	Total Amps
Design Flow					Max. 10 Amps
Design Head					

Menu Settings:

Item	Setting
OUTDOOR DESIGN	
MIX 1 MODE	
MIX 1 TERMINAL	
MIX 1 INDOOR	
MIX 1 DESIGN	
MIX 1 MINIMUM	
MIX 1 MAXIMUM	
MIX 1 MOTOR	
MIX 2 TERMINAL	
MIX 2 INDOOR	
MIX 2 DESIGN	
MIX 2 MINIMUM	
MIX 2 MAXIMUM	
MIX 2 MOTOR	
BOILER TERMINAL	
BOILER INDOOR	
BOILER DESIGN	

Item	Setting
BOILER MINIMUM	
BOILER MAXIMUM	
FIRE DELAY	
BOILER DIFFERENTIAL	
BOILER MOTOR	
MINIMUM MODULATION	
MAXIMUM MODULATION	
CYCLE LENGTH	
SCHEDULE	
DHW MODE	
DHW EXCHANGE OCCUPIED	
DHW EXCHANGE UNOCCUPIED	
SETPOINT MODE	
SETPOINT OCCUPIED	
SETPOINT UNOCCUPIED	
WWSD OCCUPIED	
WWSD UNOCCUPIED	

Blank job records can be downloaded from the tekmar website at <http://www.tekmarcontrols.com>



tekmar Control Systems Ltd., Canada
 tekmar Control Systems, Inc., U.S.A.
Head Office: 5100 Silver Star Road
Vernon, B.C. Canada V1B 3K4
(250) 545-7749 Fax. (250) 545-0650
Web Site: www.tekmarcontrols.com

