PATENTED

Engineering Specification


| tractor |
|--------------------|
| roval |
| tractor's P.O. No. |
| resentative |
| t |

FD-1290-PR-60

PVC Adjustable Floor Drain with Integrated Level

Specification

Watts Pronto!® FD-1290-PR-60 on grade PVC floor drain with anchor flange, weepholes, post-pour adjustable round heel proof stainless steel strainer with integrated bubble level, leveling shims, and PVC socket outlet.



| Strainer | | | | | | | | |
|----------|-------------------------------|--|--|--|--|--|--|--|
| Suffix | Description | | | | | | | |
| PR5 | 5"(127) Dia., Stainless Steel | | | | | | | |
| PR6 | 6"(152) Dia., Stainless Steel | | | | | | | |
| PR7 | 7"(178) Dia., Stainless Steel | | | | | | | |
| PR8 | 8"(203) Dia., Stainless Steel | | | | | | | |

| Options | | | | | | | | |
|---------|---------------------------------|--|--|--|--|--|--|--|
| Suffix | Description | | | | | | | |
| -6 | Vandal Proof | | | | | | | |
| -7 | Trap Primer Tapping | | | | | | | |
| -8 | Backwater Valve (2, 3, 4" Only) | | | | | | | |
| -F4-50 | 4" Round Cast Iron Funnel | | | | | | | |
| -F4-1 | 4" Round Nickel Bronze Funnel | | | | | | | |
| -F6-1 | 6" Round Nickel Bronze Funnel | | | | | | | |
| -G-50 | 4x9" Oval Cast Iron Funnel | | | | | | | |
| -G-1 | 4x9" Oval Nickel Bronze Funnel | | | | | | | |

Chart A


| Str. | | | Load Rat- | Free Area | Chart | В |
|---------|--------------|-------------|--------------|--------------|---------|-------------|
| Size | Min. | Max. | ax. ing Sq. | Sq. In. | Pipe | 60/ |
| 5"(127) | 1 1/2"(38) | 3 1/4"(83) | MD | 6 | Size | PVC |
| 6"(152) | 1 1/2"(38) | 3 1/4"(83) | LD | 11 | 2"(51) | 4 1/2"(114) |
| 7"(178) | 1 9/16"(40) | 3 5/16"(84) | LD | 13 | 3"(76) | 4 1/2"(114) |
| 8"(203) | 1 11/16"(43) | 3 7/16"(87) | MD | 19 | 4"(102) | 4 1/2"(114) |


NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.









Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com